



# Halogen Classic P45

## Halogen Classic 28W B22 240V P45 1CT/15 SRP

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

### Product data

General Information	
Cap base	B22 [B22]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 h
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 h
Lighting Technology	Halogen

Light Technical	
Luminous Flux	370 lm
Correlated Colour Temperature	2800 K
Luminous efficacy (rated) (nom.)	12.4 lm/W
Colour rendering index (CRI)	100

Operating and Electrical	
Power Consumption	28 W
Lamp current (nom.)	0.12 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light	Instant full light s
Power Factor (Fraction)	1
Voltage (nom.)	240 V

Voltage (nom.)	240 V
----------------	-------


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	P45 [P 45 mm]

Product Data	
Order product name	Halogen 28W B22 240V P45 1CT/15 SRP
Full product name	Halogen Classic 28W B22 240V P45 1CT/15 SRP
Full EOC	872790086296602
Order code	86296602
Material no. (12 NC)	925648645504
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8727900862966
Numerator – packs per outer box	15
EAN/UPC - Case	8718696462577

## Halogen Classic P45

### Dimensional drawing



Product	D (max)	C (max)
Halogen 28W B22 240V P45 1CT/15 SRP	46 mm	72.5 mm

