



Essential MV MR16 Alu

ESS MR16 ESS 50W GU10 240V 60D 2PF/6

The Essential MV MR16 Alu is part of the Philips "Value for Money" ranges. It is ideal for professional end-users looking for accent light - without a transformer - to create contrast in shops, hotels and restaurants.

Product data


General Information	
Cap-Base	GU10 [GU10]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 h
Rated Lifetime (Hours)	2,000 h
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	60 degree(s)
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	50 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	240 V
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	MR16 [2inch/50mm]
Product Data	
Order product name	ESS MR16 ESS 50W GU10 240V 60D 2PF/6
Full product name	ESS MR16 ESS 50W GU10 240V 60D 2PF/6
Full product code	871150099376201
Local code description	ESSGU1050W
Order code	925649245501
Material Nr. (12NC)	925649245501
Local order code	ESSGU1050W
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500993762
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291228080

Datasheet, 2023, December 18 data subject to change

Essential MV MR16 Alu

Dimensional drawing



Product	D (max)	C (max)
ESS MR16 ESS 50W GU10 240V 60D 2PF/6	50.7 mm	46 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.