



Halogen Classic A-shape

EcoClassic 53W E27 230V A55 CL 1CT/15

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Luminous Flux	850 lm
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	16.0 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	53.0 W
Lamp Current (Nom)	0.23 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A55 [A 55mm]

Approval and Application	
Energy Consumption kWh/1000 h	53 kWh

Product Data	
Order product name	EcoClassic 53W E27 230V A55 CL 1CT/15
Full product name	EcoClassic 53W E27 230V A55 CL 1CT/15
Full product code	871869646638400
Order code	925693144251
Material Nr. (12NC)	925693144251
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696466384
Numerator - Packs per outer box	15
EAN/UPC - Case	8718696466391

Halogen Classic A-shape

Dimensional drawing



Product	D (max)	C (max)
EcoClassic 53W E27 230V A55 CL 1CT/15	56 mm	97 mm

