



Halogen Classic A-shape

Halogen Classic 70W B22 240V A55 1CT/15 SRP

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Product data


| General Information | |
|------------------------------------|----------------------------------|
| Cap-Base | B22 [B22] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 2,000 hour(s) |
| Switching Cycle | 8,000 |
| Rated Lifetime (Hours) | 2,000 hour(s) |
| Lighting Technology | Halogen |
| Light Technical | |
| Luminous Flux | 1,200 lm |
| Correlated Color Temperature (Nom) | 2800 K |
| Luminous Efficacy (rated) (Nom) | 17.1 lm/W |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 70.0 W |
| Lamp Current (Nom) | 0.29 A |
| Starting Time (Nom) | 0.0 s |
| Warm-up time to 60% light | instant full light s |
| Power Factor (Fraction) | 1 |
| Voltage (Nom) | 240 V |
| Voltage (Nom) | 240 V |

| Controls and Dimming | |
|-------------------------------|--------------|
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Shape | A55 [A 55mm] |
| Approval and Application | |
| Energy Consumption kWh/1000 h | 70 kWh |

| Product Data | |
|---------------------------------|---|
| Order product name | Halogen 70W B22 240V A55 1CT/15 SRP |
| Full product name | Halogen Classic 70W B22 240V A55 1CT/15 SRP |
| Full product code | 872790025189002 |
| Order code | 25189002 |
| Material Nr. (12NC) | 925700845506 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8727900251890 |
| Numerator - Packs per outer box | 15 |
| EAN/UPC - Case | 8718696462362 |

Halogen Classic A-shape

Dimensional drawing



| Product | D (max) | C (max) |
|-------------------------------------|---------|---------|
| Halogen 70W B22 240V A55 1CT/15 SRP | 56 mm | 95.5 mm |

