



Halogen Classic A-shape

EcoClassic 105W B22 240V A55 FR 1CT/10

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Product data

General Information	
Cap-Base	B22 [B22]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Luminous Flux	1,980 lm
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	18.9 lm/W
Color rendering index (CRI)	100


Operating and Electrical	
Power Consumption	105 W
Lamp Current (Nom)	0.44 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	240 V

Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A55 [A 55mm]

Product Data	
Order product name	EcoClassic 105W B22 240V A55 FR 1CT/10
Full product name	EcoClassic 105W B22 240V A55 FR 1CT/10
Full product code	872790093552300
Order code	925702745503
Material Nr. (12NC)	925702745503
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900935523
Numerator - Packs per outer box	10
EAN/UPC - Case	8727900935530

Halogen Classic A-shape

Dimensional drawing



Product	D (max)	C (max)
EcoClassic 105W B22 240V A55 FR 1CT/10	56 mm	95.5 mm

