



# Halogen PAR

## Halogen 39PAR30S/EVP/FL25 120V 15/1

Halogen PAR lamps reduce energy consumption without sacrificing the qualities of a traditional PAR lamp. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar PAR20, PAR30S, PAR30L, and PAR38 shapes. Use them in existing fixtures just as you would standard halogen PAR lamps.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	1,100 hour(s)
Lighting Technology	Halogen

  

Light Technical	
Beam Angle (Nom)	25 degree(s)
Luminous Flux	530 lm
Luminous Intensity (Nom)	2,250 cd
Color rendering index (CRI)	100

  

Operating and Electrical	
Power Consumption	39 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Reflector Finish	Aluminized
Bulb Shape	PAR30S [PAR 3.75 inch/95mm Short]

  

Product Data	
Order product name	39PAR30S/EVP/FL25 120V 15/1
Full product name	Halogen 39PAR30S/EVP/FL25 120V 15/1
Order code	428960
Material Nr. (12NC)	925709736302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677428969
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677428964

# Halogen PAR

## Dimensional drawing

### Product

39PAR30S/EVP/FL25 120V 15/1

