



# Essential LV MR16

## ESSPlus MR16 35W GU5.3 12V 60D 2CT/10

The Essential LV MR16 is part of the Philips "Value for Money" ranges. It is a good choice for professional end-users looking for high-quality accent light to create contrast in shops, hotels and restaurants.

### Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	3,000 h
Rated Lifetime (Hours)	3,000 h
Lighting Technology	Halogen

Light Technical	
Beam Angle (Nom)	60 degree(s)
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	35 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]

Product Data	
Order product name	ESSPlus MR16 35W GU5.3 12V 60D 2CT/10
Full product name	ESSPlus MR16 35W GU5.3 12V 60D 2CT/10
Full product code	871829121885200
Local code description	13122
Order code	925711917101
Material Nr. (12NC)	925711917101
Local order code	13122
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291218852
Numerator - Packs per outer box	10
EAN/UPC - Case	8718291218869

## Essential LV MR16

### Dimensional drawing



Product	D (max)	C (max)
ESSPlus MR16 35W GU5.3 12V 60D 2CT/10	50.7 mm	46 mm

