



Capsules LV 3,000 h

Caps 3000h 7W G4 12V CL 1CT/10x10F

Low-voltage halogen capsule. Ideal solution for small decorative luminaires. The UV-block glass and low-pressure filling allow usage without cover glass. The compact halogen capsule delivers crisp white light over a long lifetime.

Product data

General Information	
Cap base	G4 [G4]
Operating position	UNIVERSAL [Any/Universal]
Nominal lifetime (nom.)	3000 h
Switching cycle	12000X
Light Technical	
Luminous flux (nom.)	86 lm
Luminous flux (rated) (nom.)	86 lm
Luminous efficacy (rated) (nom.)	12.3 lm/W
Color rendering index (nom.)	100
Operating and Electrical	
Power (Rated) (Nom)	7.0 W
Lamp current (nom.)	0.58 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light s
Power factor (nom.)	1
Voltage (Nom)	12 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb finish	Clear
Approval and Application	
Energy efficiency label (EEL)	B
Energy Consumption kWh/1000 h	7 kWh
Luminaire Design Requirements	
Bulb temperature (max.)	600 °C
Pinch temperature (max.)	350 °C
Product Data	
Full product code	871869682786400
Order product name	Caps 3000h 7W G4 12V CL 1CT/10x10F
EAN/UPC – product	8718696827864
Order code	82786400
Numerator – quantity per pack	1
Numerator – packs per outer box	100
Material no. (12NC)	925723217101
Net weight (piece)	0.002 kg

Capsules LV 3,000 h

Dimensional drawing

D

Product	D (max)	L	C (max)
Caps 3000h 7W G4 12V CL 1CT/10x10F	10 mm	22.2 mm	33 mm

EcoHalo Capsule G4 12v7w CL B3000

