



# Capsules LV 3000 h



## Caps 3000h 25W GY6.35 12V CL 1CT/10x10F

Low-voltage halogen capsule. Ideal solution for small decorative luminaires. UV-block glass and low-pressure filling allow usage without cover glass. The compact halogen capsule delivers crisp white light over a long lifetime.

### Product data

General Information	
Cap-Base	GY6.35
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	3,000 hour(s)
Switching Cycle	12,000
Rated Lifetime (Hours)	3,000 hour(s)
Lighting Technology	Halogen
Flux measurement reference	Sphere

Light Technical	
Luminous Flux	500 lm
Chromaticity Coordinate X (Nom)	0.444
Chromaticity Coordinate Y (Nom)	0.407
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	20 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	26 W
Lamp Current (Nom)	2.083 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	Instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	12 V

Voltage (Nom)	12 V
---------------	------

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T11

Approval and Application	
Energy Efficiency Class	G
Energy Consumption kWh/1000 h	26 kWh
EPREL Registration Number	423253

Product Data	
Order product name	Caps 3000h 25W GY6.35 12V CL 1CT/10x10F
Full product name	Caps 3000h 25W GY6.35 12V CL 1CT/10x10F
Full product code	871869682780200
Order code	82780200
Material Nr. (12NC)	925723617101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696827802
Numerator - Packs per outer box	100
EAN/UPC - Case	8718696827826

# Capsules LV 3000 h

## Dimensional drawing



Product	D (max)	L	C (max)
Caps 3000h 25W GY6.35 12V CL 1CT/10x10F	12 mm	30 mm	44 mm

