



# Capsules LV 3,000 h



## Caps 3000h 25W GY6.35 12V CL 1CT/10x10F

Low-voltage halogen capsule. Ideal solution for small decorative luminaires. The UV-block glass and low-pressure filling allow usage without cover glass. The compact halogen capsule delivers crisp white light over a long lifetime.

### Product data

General Information	
Cap base	GY6.35 [GY6.35]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	3,000 h
Switching Cycle	12,000
Rated Lifetime (Hours)	3,000 h
Lighting Technology	Halogen
Flux measurement reference	Sphere

Light Technical	
Luminous Flux	500 lm
Chromaticity Coordinate X (Nom)	0.444
Chromaticity Coordinate Y (Nom)	0.407
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	20 lm/W
Colour rendering index (CRI)	100

Operating and Electrical	
Power Consumption	26 W
Lamp current (nom.)	2.083 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light	Instant full light s
Power Factor (Fraction)	1
Voltage (nom.)	12 V

Voltage (nom.)	12 V
----------------	------

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T11 [T 11 mm]

Approval and Application	
Energy Efficiency Class	G
Energy consumption kWh/1,000 hours	26 kWh
EPREL registration number	423253

Product Data	
Order product name	Caps 3000h 25W GY6.35 12V CL 1CT/10x10F
Full product name	Caps 3000h 25W GY6.35 12V CL 1CT/10x10F
Full EOC	871869682780200
Order code	82780200
Material no. (12 NC)	925723617101
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696827802
Numerator – packs per outer box	100
EAN/UPC - Case	8718696827826

# Capsules LV 3,000 h

## Dimensional drawing



Product	D (max)	L	C (max)
Caps 3000h 25W GY6.35 12V CL 1CT/10x10F	12 mm	30 mm	44 mm

