



LV Halogen Oven Capsules



Caps OV 20W G4 12V 1CT/50

Halogen capsules ideal as replacement lamp for many specific oven types. Resistant to high temperatures, perfectly fitting oven application.

Product data

General Information	
Cap-Base	G4
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Flux measurement reference	Sphere
Light Technical	
Luminous Flux	320 lm
Chromaticity Coordinate X (Nom)	0.452
Chromaticity Coordinate Y (Nom)	0.409
Correlated Color Temperature (Nom)	2850 K
Luminous Efficacy (rated) (Nom)	16 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	22 W
Lamp Current (Nom)	1.66 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	Instant full light s


Power Factor (Fraction)	1
Voltage (Nom)	12 V
Voltage (Nom)	12 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T9
Approval and Application	
Energy Efficiency Class	G
Energy Consumption kWh/1000 h	22 kWh
EPREL Registration Number	423259
Product Data	
Order product name	Caps OV 20W G4 12V 1CT/50
Full product name	Caps OV 20W G4 12V 1CT/50
Full product code	871869961323500
Order code	61323500
Material Nr. (12NC)	925723817101

LV Halogen Oven Capsules

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699613235
Numerator - Packs per outer box	50

EAN/UPC - Case	8718699613242
----------------	---------------

Dimensional drawing



Product	D (max)	L	C (max)
Caps OV 20W G4 12V 1CT/50	10 mm	22.2 mm	33 mm

