





MV Halogen Oven Capsules

Caps OV 25W G9 230V 1CT/20

Halogen capsules ideal as replacement lamp for many specific oven types. Resistant to high temperatures, perfectly fitting oven application.

Product data

General Information		
Cap-Base	G9	
Operating Position	UNIVERSAL [Any or Universal (U)]	
Nominal lifetime	2,000 hour(s)	
Rated Lifetime (Hours)	2,000 hour(s)	
Lighting Technology	Halogen	
Flux measurement reference	Sphere	
Light Technical		
Luminous Flux	250 lm	
Chromaticity Coordinate X (Nom)	0.468	
Chromaticity Coordinate Y (Nom)	0.412	
Correlated Color Temperature (Nom)	2650 K	
Color rendering index (CRI)	100	
Operating and Electrical		
Power Consumption	26 W	
Lamp Current (Nom)	0.11 A	
Starting Time (Nom)	0.0 s	
Power Factor (Fraction)	1	
Voltage (Nom)	230 V	

Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	Т11
Approval and Application	
Energy Efficiency Class	G
Energy Consumption kWh/1000 h	26 kWh
EPREL Registration Number	423260
Product Data	
Order product name	Caps OV 25W G9 230V 1CT/20
Full product name	Caps OV 25W G9 230V 1CT/20
Full product code	871869961321100
Order code	61321100
Material Nr. (12NC)	925723944201
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699613211

MV Halogen Oven Capsules

Numerator - Packs per outer box	20
EAN/UPC - Case	8718699613228

Dimensional drawing



Product	D (max)	C (max)
Caps OV 25W G9 230V 1CT/20	12.75 mm	44.6 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, August 28 - data subject to change