



# Standard Candle B35 clear

Stan 60W E14 230V B35 CL 1CT/10X10F

Flame-shaped bulb with clear glass and vacuum- or gas-filled bulb with B- or E- base

Product data

General Information	
Cap-Base	E14
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	670 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	B35
Product Data	
Order product name	Stan 60W E14 230V B35 CL 1CT/10X10F
Full product name	Stan 60W E14 230V B35 CL 1CT/10X10F
Full product code	871150001167150
Order code	926000003017
Material Nr. (12NC)	926000003017
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500011671
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500075239

Standard Candle B35 clear

Dimensional drawing



Product	D	C (max)
Stan 60W E14 230V B35 CL 1CT/10X10F	35 mm	100 mm

