



Standard Lustre P45 frosted

STAN 60W E14 230V P45 FR 1CT/10X10F

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E-base


Product data

General Information	
Cap-Base	E14
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	650 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P45
Approval and Application	
Energy Consumption kWh/1000 h	60 kWh
Product Data	
Order product name	Stan 60W E14 230V P45 FR 1CT/10X10F
Full product name	STAN 60W E14 230V P45 FR 1CT/10X10F
Full product code	871150006757950
Order code	06757950
Material Nr. (12NC)	926000003857
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500067579
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500084392

Standard Lustre P45 frosted

Dimensional drawing



Product	D	C (max)
Stan 60W E14 230V P45 FR 1CT/10X10F	45 mm	78 mm

