



Standard A-shape frosted

STAN 75W E27 230V A55 FR 1CT/12X10F

Conventional pear-shaped incandescent lamps

Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	930 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	75 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A55 [A 55mm]
Product Data	
Order product name	Stan 75W E27 230V A55 FR 1CT/12X10F
Full product name	STAN 75W E27 230V A55 FR 1CT/12X10F
Full product code	871150035474784
Order code	35474784
Material Nr. (12NC)	926000004003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500354747
Numerator - Packs per outer box	120
EAN/UPC - Case	8711500354761

Standard A-shape frosted

Dimensional drawing



Product	D (max)	D	C (max)
Stan 75W E27 230V A55 FR 1CT/12X10F	56 mm	55 mm	97 mm

