



Standard A-shape clear

STAN 75W E27 230V A55 CL 1CT/12X10F

Conventional pear-shaped incandescent lamps

Product data

General Information	
Cap base	E27 [E27]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime (nom.)	1000 h

Light Technical	
Luminous flux (nom.)	930 lm
Color rendering index (nom.)	100

Operating and Electrical	
Power (Rated) (Nom)	75 W
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb finish	Clear

Approval and Application	
Energy efficiency label (EEL)	E

Product Data	
Full product code	871150035459484
Order product name	Standard 75W E27 230V A55 CL 1CT/12X10F
EAN/UPC – product	8711500354594
Order code	35459484
Numerator – quantity per pack	1
Numerator – packs per outer box	120
Material no. (12NC)	926000004004
Net weight (piece)	0.025 kg
ILCOS Code	IAA/C-75-230-E27-55

Standard A-shape clear

Dimensional drawing



STD 75W E27 230V A55 CL

Product

Standard 75W E27 230V A55 CL 1CT/12X10F

