



Standard A-shape clear

Standard 100W E27 240V A55 CL 1CT/10X10F

Conventional pear-shaped incandescent lamps

Product data

General Information	
Cap base	E27 [E27]
Burning Position	UNIVERSAL [Any/Universal]
Nominal lifetime (nom.)	1000 h

Light Technical	
Lamp Luminous Flux 25°C EL (Nom)	1320 lm
Colour Rendering Index,horiz (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	100 W
Voltage (Nom)	240 V

Controls and Dimming	
Dimmable	yes


Mechanical and Housing	
Bulb finish	Clear

Approval and Application	
Energy efficiency label (EEL)	E

Product Data	
Full product code	871829174675100
Order product name	Standard 100W E27 240V A55 CL 1CT/10X10F
EAN/UPC – product	8718291746751
Order code	74675100
Numerator – quantity per pack	1
Numerator – packs per outer box	100
Material no. (12NC)	926000004009
Net weight (piece)	25.000 g
ILCOS Code	IAA/C-100-240-E27-55

Standard A-shape clear

Dimensional drawing



Product

Standard 100W E27 240V A55 CL 1CT/10X10F

STD 100W E27 240V A55 CL

