



Standard A-shape clear

Stan 100W E27 240V A55 CL 1CT/10X10F

Conventional pear-shaped incandescent lamps

Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	1,320 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	100 W
Voltage (Nom)	240 V
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A55 [A 55mm]
Product Data	
Order product name	Stan 100W E27 240V A55 CL 1CT/10X10F
Full product name	Stan 100W E27 240V A55 CL 1CT/10X10F
Full product code	871829174675100
Order code	926000004009
Material Nr. (12NC)	926000004009
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291746751
Numerator - Packs per outer box	100
EAN/UPC - Case	8718291746775

Standard A-shape clear

Dimensional drawing



Product	D (max)	D	C (max)
Stan 100W E27 240V A55 CL 1CT/10X10F	56 mm	55 mm	97 mm

