



Standard Lustre P45 clear

STAN 60W E27 230V P45 CL 1CT/10X10F

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E-base


Product data

General Information	
Cap-Base	E27
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	640 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45
Product Data	
Order product name	Stan 60W E27 230V P45 CL 1CT/10X10F
Full product name	STAN 60W E27 230V P45 CL 1CT/10X10F
Full product code	871150006702950
Order code	06702950
Material Nr. (12NC)	926000005857
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500067029
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500082381

Standard Lustre P45 clear

Dimensional drawing



Product	D	C (max)
Stan 60W E27 230V P45 CL 1CT/10X10F	45 mm	73 mm

