PHILIPS Lighting



Reflector diam 63 mm

Reflector 60W E27 230V NR63 30D FR 1CT/30

Reflector lamps based on advanced spotlighting technology

Product data

General Information	
Cap-Base	E27
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	30 degree(s)
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	

Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	NR63
Product Data	
Order product name	Refl 60W E27 230V NR63 30D FR 1CT/30
Full product name	Reflector 60W E27 230V NR63 30D FR 1CT/30
Full product code	871150004366578
Order code	04366578
Material Nr. (12NC)	92600005918
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500043665
Numerator - Packs per outer box	30
EAN/UPC - Case	8711500343994

Reflector diam 63 mm

Dimensional drawing



 Product
 D

 Refl 60W E27 230V NR63 30D FR 1CT/30
 63 mm

Photometric data



Light Distribution Diagram - Refl 60W E27 230V NR63 30D FR 1CT/30



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 14 - data subject to change