



Reflector diam 63 mm

REFL 40W E27 230V NR63 30D 1CT/30

Reflector lamps based on advanced spotlighting technology

Product data

General Information	
Base	E27 [E27]
Operating Position	Universal [Universal]
Nominal Lifetime (Nom)	1000 h

Light Technical	
Beam Angle (Nom)	30 °
Luminous Intensity (Max)	420 cd
Rated Beam Angle	30 °
Color Rendering Index (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	40 W
Voltage (Nom)	230 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted

Product Data	
Order product name	Reflector 40W E27 230V NR63 30D 1CT/30
EAN/UPC - Product	8711500043603
Order code	250837
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	926000006213
Net Weight (Piece)	25.970 g
ILCOS Code	IRR/F-40-230-E27-63/30

Reflector diam 63 mm

Dimensional drawing



Product

Reflector 40W E27 230V NR63 30D 1CT/30

REF SPOT 40W E27 230V NR63 30D FR

