



Standard Lustre P45 clear

STAN 40W E14 230V P45 CL 1CT/10X10F

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base

Product data

General Information	
Cap base	E14 [E14]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime (nom.)	1000 h

Light Technical	
Luminous flux (nom.)	405 lm
Color rendering index (nom.)	100

Operating and Electrical	
Power (Rated) (Nom)	40 W
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb finish	Clear


Cap base information	na [-]
Filament shape	-

Approval and Application	
Energy efficiency label (EEL)	E

Product Data	
Full product code	871150001186250
Order product name	Standard 40W E14 230V P45 CL 1CT/10X10F
EAN/UPC – product	8711500011862
Order code	01186250
Numerator – quantity per pack	1
Numerator – packs per outer box	100
Material no. (12NC)	926000006511
Net weight (piece)	0.015 kg
ILCOS Code	IBP/C-40-230-E14-45

Standard Lustre P45 clear

Dimensional drawing



LUS STD 40W E14 230V P45 CL

Product	D	C (max)
Standard 40W E14 230V P45 CL 1CT/10X10F	45 mm	78 mm

