



Standard Lustre P45 frosted

STAN 40W E27 230V P45 FR 1CT/10X10F

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E-base


Product data

General Information	
Cap-Base	E27
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	390 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P45
Product Data	
Order product name	Stan 40W E27 230V P45 FR 1CT/10X10F
Full product name	STAN 40W E27 230V P45 FR 1CT/10X10F
Full product code	871150001122050
Order code	01122050
Material Nr. (12NC)	926000007412
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500011220
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500084125

Standard Lustre P45 frosted

Dimensional drawing



Product	D	C (max)
Stan 40W E27 230V P45 FR 1CT/10X10F	45 mm	73 mm

