



Standard Candle B35 clear

Stan 40W E14 230V B35 CL U 1CT/6X50CT

Flame-shaped bulb with clear glass and vacuum- or gas-filled bulb with B- or E-base

Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	410 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	B35 [B 35mm]
Product Data	
Order product name	Stan 40W E14 230V B35 CL U 1CT/6X50CT
Full product name	Stan 40W E14 230V B35 CL U 1CT/6X50CT
Full product code	890143700484000
Order code	926000205010
Material Nr. (12NC)	926000205010
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8901437004840
Numerator - Packs per outer box	300
EAN/UPC - Case	8727900076974

Standard Candle B35 clear

Dimensional drawing



Product	D	C (max)
Stan 40W E14 230V B35 CL U 1CT/6X50CT	35 mm	100 mm

