



Standard Candle B35 clear

Standard 40W E14 230V B35 CL U 1CT/6X50CT


Flame-shaped bulb with clear glass and vacuum- or gas-filled bulb with B- or E-base

Product data

General Information		Approval and Application	
Cap-Base	E14 [E14]	Energy Efficiency Label (EEL)	E
Operating Position	UNIVERSAL [Universal]	Product Data	
Nominal Lifetime (Nom)	1000 h	Full product code	890143700484000
Light Technical		Order product name	Standard 40W E14 230V B35 CL U 1CT/6X50CT
Luminous Flux (Nom)	410 lm	EAN/UPC - Product	8901437004840
Color Rendering Index (Nom)	100	Order code	926000205010
Operating and Electrical		Numerator - Quantity Per Pack	1
Power (Rated) (Nom)	40 W	Numerator - Packs per outer box	300
Voltage (Nom)	230 V	Material Nr. (12NC)	926000205010
Controls and Dimming		Net Weight (Piece)	0.015 kg
Dimmable	Yes	ILCOS Code	IBB/C-40-230-E14-35
Mechanical and Housing			
Bulb Finish	Clear		

Standard Candle B35 clear

Dimensional drawing



Product	D	C (max)
Standard 40W E14 230V B35 CL U 1CT/6X50CT	35 mm	100 mm

CAN STD 40W E14 230V B35 CL

