



Softone Standard T-shape

Softone 40W B22 230V T55 WH U 1CT/100

T-shaped gas-filled lamps with a modern appearance

Product data

General Information	
Cap-Base	B22 [B22]
Operating Position	UNIVERSAL [Universal]
Nominal Lifetime (Nom)	1000 h

Light Technical	
Luminous Flux (Nom)	370 lm
Color Rendering Index (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	40 W
Voltage (Nom)	230 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Soft White

Product Data	
Full product code	890143700490100
Order product name	Softone 40W B22 230V T55 WH U 1CT/100
EAN/UPC - Product	8901437004901
Order code	926000205013
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	926000205013
Net Weight (Piece)	0.028 kg
ILCOS Code	IAT/W-40-230-B22d-55

Softone Standard T-shape

Dimensional drawing



Product

Softone 40W B22 230V T55 WH U 1CT/100

STD SOFT 40W B22 230V T55 SW

