



Softone Standard T-shape

Soft 100W B22 230V T55 WH U 1CT/100

T-shaped gas-filled lamps with a modern appearance


Product data

General Information	
Cap-Base	B22 [B22]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	1,200 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	100 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Soft White
Bulb Shape	T55 [T 55mm]
Product Data	
Order product name	Soft 100W B22 230V T55 WH U 1CT/100
Full product name	Soft 100W B22 230V T55 WH U 1CT/100
Full product code	890143700492500
Order code	926000205014
Material Nr. (12NC)	926000205014
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8901437004925
Numerator - Packs per outer box	100
EAN/UPC - Case	8727900077018

Softone Standard T-shape

Dimensional drawing



Product	D	C (max)
Soft 100W B22 230V T55 WH U 1CT/100	55 mm	93.5 mm

