



# Accentline

## Accentline 35W 4000h GU5.3 12V 36D 1CT/10X5F

Low-voltage halogen burner optically positioned in a glass reflector with and without front glass

### Product data

| General Information        |                                  |
|----------------------------|----------------------------------|
| Cap-Base                   | GU5.3                            |
| Operating Position         | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime           | 4,000 hour(s)                    |
| Switching Cycle            | 16,000                           |
| Rated Lifetime (Hours)     | 4,000 hour(s)                    |
| Lighting Technology        | Halogen                          |
| Life to 50% Failures (Nom) | 4,000 hour(s)                    |

| Light Technical                    |              |
|------------------------------------|--------------|
| Beam Angle (Nom)                   | 36 degree(s) |
| Luminous Flux                      | 430 lm       |
| Correlated Color Temperature (Nom) | 3000 K       |
| Color rendering index (CRI)        | 100          |
| Luminous Flux in 90° Cone (Rated)  | 430 lm       |

| Operating and Electrical  |                      |
|---------------------------|----------------------|
| Power Consumption         | 35 W                 |
| Starting Time (Nom)       | 0.0 s                |
| Warm-up time to 60% light | Instant full light s |
| Voltage (Nom)             | 12 V                 |
| Voltage (Nom)             | 12 V                 |


| Controls and Dimming |     |
|----------------------|-----|
| Dimmable             | Yes |

| Mechanical and Housing |      |
|------------------------|------|
| Bulb Shape             | MR16 |

| Approval and Application      |        |
|-------------------------------|--------|
| Energy Consumption kWh/1000 h | 37 kWh |

| Product Data                    |                                              |
|---------------------------------|----------------------------------------------|
| Order product name              | Accent 35W 4000h GU5.3 12V 36D 1CT/10X5F     |
| Full product name               | Accentline 35W 4000h GU5.3 12V 36D 1CT/10X5F |
| Full product code               | 871869658842000                              |
| Order code                      | 58842000                                     |
| Material Nr. (12NC)             | 926000850062                                 |
| Numerator - Quantity Per Pack   | 1                                            |
| EAN/UPC - Product/Case          | 8718696588420                                |
| Numerator - Packs per outer box | 50                                           |
| EAN/UPC - Case                  | 8718696588444                                |

Dimensional drawing



| Product                                  | D (max) | C (max) |
|------------------------------------------|---------|---------|
| Accent 35W 4000h GU5.3 12V 36D 1CT/10X5F | 51 mm   | 46 mm   |

