



Accentline

Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F

Low-voltage halogen burner optically positioned in a glass reflector with and without front glass

Product data

General Information	
Cap base	GU5.3 [GU5.3]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	4,000 h
Switching Cycle	16,000
Rated Lifetime (Hours)	4,000 h
Lighting Technology	Halogen
Life to 50% failures (nom.)	4,000 h

Light Technical	
Beam angle (nom.)	36 degree(s)
Luminous Flux	680 lm
Correlated Colour Temperature	3000 K
Colour rendering index (CRI)	100
Luminous flux in 90° cone (rated)	680 lm

Operating and Electrical	
Power Consumption	50 W
Starting time (nom.)	0.0 s
Warm-up time to 60% light	Instant full light s
Voltage (nom.)	12 V
Voltage (nom.)	12 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb shape	MR16 [2 inch/50 mm]

Approval and Application	
Energy consumption kWh/1,000 hours	53 kWh

Product Data	
Order product name	Accent 50W 4000h GU5.3 12V 36D 1CT/10X5F
Full product name	Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F
Full EOC	871869658845100
Order code	58845100
Material no. (12 NC)	926000850063
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696588451
Numerator – packs per outer box	50
EAN/UPC - Case	8718696588475

Dimensional drawing



Product	D (max)	C (max)
Accent 50W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm

