



T5 Retail Sales

F4T5/SOFT WHITE/6" 12/1PK

Available in a variety of lengths and lumen packages, these T5 lamps are an ideal solution for use in compact fixtures.

Warnings and Safety

- CAUTION: When changing lamps, turn off power to the fixture to avoid electric shock.
- Fluorescent lamps can shatter if broken.
- Handle with care and store in a safe place.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G5 [G5]

Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	150 lm
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	85

Operating and Electrical	
Power Consumption	4 W

Mechanical and Housing	
Bulb Shape	T-5 (T5)

Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg

Product Data	
Order product name	F4T5/SOFT WHITE/6" 12/1PK
Full product name	F4T5/SOFT WHITE/6" 12/1PK
Order code	392183
Material Nr. (12NC)	927800083003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677392185
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677392180

T5 Retail Sales

Dimensional drawing

Product

F4T5/SOFT WHITE/6" 12/1PK

