



Preheat T8

F30T8/CW ALTO 30PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	7500 h
Life with 3 Hour Per Day Use	3 a
Features	ALTO® (ALTO)

Light Technical	
Color Code	33
Luminous Flux (Nom)	2200 lm
Color Designation	Cool White (CW)
Design Mean Lumens	1760 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	62

Operating and Electrical	
Power (Rated) (Nom)	30 W

Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	36
-----------------------	----

Approval and Application	
Picogram Per Lumen Hour	144 pg/lm.h
Mercury (Hg) Content (Nom)	1.9 mg

Product Data	
Order product name	F30T8/CW ALTO 30PK
EAN/UPC - Product	046677281472
Order code	281477
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927825403326
Net Weight (Piece)	0.001 kg

Preheat T8

Dimensional drawing

Product

F30T8/CW ALTO 30PK

F30T8/33 36 ALTO

