



T8 Standard

F17T8/TL835/ALTO 30PK

Philips T8 lamps are energy-efficient lighting solutions.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	36000 h
Life 12-Hr Instant Start [Hrs]	30000 h
Life 3-Hr Program Start [Hrs]	30000 h
Life 3-Hr Instant Start [Hrs]	24000 h
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL835 [CCT of 3500K (835)]
Luminous Flux (Nom)	1375 lm
Color Designation	TL835
Design Mean Lumens	1310 lm
Correlated Color Temperature (Nom)	3500 K
Color Rendering Index (Nom)	85
Operating and Electrical	
Power (Rated) (Nom)	17 W

Mechanical and Housing	
Cap-Base Information	Green Base
Nominal Length (Inch)	24
Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	54 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg

Product Data	
Order product name	F17T8/TL835/ALTO 30PK
EAN/UPC - Product	046677281885
Order code	281881
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927850083503
Net Weight (Piece)	0.068 kg

T8 Standard

Dimensional drawing

Product

F17T8/TL835/ALTO 30PK



F17T8/835 24 ALTO ES

