



MASTER TL-D Super 80

TLDRS16W-S85ECO 25PK

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Approval and Application	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Energy Saving Product	Energy Saving
Features	ALTO® (ALTO)	Mercury (Hg) Content (Nom)	1.7 mg
Light Technical		Product Data	
Color Code	TL850 [CCT of 5000K (850)]	Order product name	TLDRS16W-S85ECO 25PK
Luminous Flux	1,300 lm	Full product name	TLDRS16W-S85ECO 25PK
Color Designation	TL850	Full product code	872790091771000
Correlated Color Temperature (Nom)	5000 K	Order code	927850085002
Color rendering index (CRI)	82	Material Nr. (12NC)	927850085002
Operating and Electrical		Numerator - Quantity Per Pack	1
Power Consumption	17 W	EAN/UPC - Product/Case	8727900917710
Mechanical and Housing		Numerator - Packs per outer box	25
Bulb Shape	T-8 (T8)	EAN/UPC - Case	8727900917727

MASTER TL-D Super 80

Dimensional drawing

Product
TLDRS16W-S85ECO 25PK

