



MASTER TL-D Super 80

TLDRS16W-S85ECO 25PK

Lâmpada fluorescente tubular de mercúrio (baixa pressão de descarga) com 26 mm de diâmetro.

Avisos e Segurança

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dados do produto

Informações gerais	
Casquilho	G13 [Medium Bi-Pin Fluorescent]
Características	ALTO® (ALTO)
Dados técnicos de luz	
Código da cor	TL850 [CCT of 5000K (850)]
Fluxo luminoso	1.300 lm
Designação da cor	TL850
Temperatura de cor correlacionada (Nom.)	5000 K
Color rendering index (CRI)	82
Dados elétricos e de operação	
Consumo de energia	17 W
Dados mecânicos e de compartimento	
Forma da lâmpada	T-8 (T8)

Aprovação e aplicação	
Produto energeticamente eficiente	Economia de energia
Conteúdo de mercúrio (Hg) (Nom.)	1,7 mg
Dados do produto	
Nome de produto da encomenda	TLDRS16W-S85ECO 25PK
Nome do produto completo	TLDRS16W-S85ECO 25PK
Full EOC	872790091771000
Descrição do código local	LAMPADA FLUOR TUBULAR TLDRS16W-S85-I
Código de encomenda	927850085002
Nº do material (12NC)	927850085002
Código local	TLDRS16W-S85-I
Numerador — Quantidade por embalagem	1
EAN/UPC - produto/caixa	8727900917710
Numerador SAP — Embalagens por exterior	25
EAN/UPC - caixa	8727900917727

MASTER TL-D Super 80

Desenho dimensional

Product
TLDRS16W-S85ECO 25PK

