



# T8 Plus

## F17T8/TL835/PLUS/ALTO 30PK

Philips PLUS T8 lamps are energy-efficient lighting solutions and offer long life.

### Product data

General Information	
Base	G13 [ Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	42000 h
Life 12-Hr Instant Start [Hrs]	36000 h
Life 3-Hr Program Start [Hrs]	36000 h
Life 3-Hr Instant Start [Hrs]	30000 h
Features	ALTO® Plus
Light Technical	
Color Code	TL835 [ CCT of 3500K (835)]
Initial lumen (Nom)	1375 lm
Color Designation	TL835
Design Mean Lumens	1310 lm
Correlated Color Temperature (Nom)	3500 K
Color Rendering Index (Nom)	85
Operating and Electrical	
Power (Rated) (Nom)	17 W

### Warnings and Safety

Mechanical and Housing	
Cap-Base Information	Green Base
Nominal Length (Inch)	24
Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	43 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg
Product Data	
Order product name	F17T8/TL835/PLUS/ALTO 30PK
EAN/UPC - Product	046677280949
Order code	280941
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927850183503
Net Weight (Piece)	0.068 kg

# T8 Plus

## Dimensional drawing

### Product

F17T8/TL835/PLUS/ALTO 30PK



F17T8/835 24 ALTO Plus ES

