



# T8 Plus

## F17T8/TL850/PLUS/ALTO 30PK

Philips PLUS T8 lamps are energy-efficient lighting solutions and offer long life.

### Product data

General Information	
Base	G13 [ Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	42000 h
Life 12-Hr Instant Start [Hrs]	36000 h
Life 3-Hr Program Start [Hrs]	36000 h
Life 3-Hr Instant Start [Hrs]	30000 h
Features	ALTO® Plus
Light Technical	
Color Code	TL850 [ CCT of 5000K (850)]
Initial lumen (Nom)	1300 lm
Color Designation	TL850
Design Mean Lumens	1235 lm
Correlated Color Temperature (Nom)	5000 K
Color Rendering Index (Nom)	82
Operating and Electrical	
Power (Rated) (Nom)	17 W

Mechanical and Housing	
Cap-Base Information	Green Base
Nominal Length (Inch)	24
Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	46 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg

Product Data	
Order product name	F17T8/TL850/PLUS/ALTO 30PK
EAN/UPC - Product	046677280963
Order code	280966
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927850185002
Net Weight (Piece)	0.068 kg


### Warnings and Safety

## T8 Plus

### Dimensional drawing

#### Product

F17T8/TL850/PLUS/ALTO 30PK



F17T8/850 24 ALTO Plus ES

