



# T8 Standard

## F25T8/TL850 ALTO 30PK

Philips T8 lamps are energy-efficient lighting solutions.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL850 [CCT of 5000K (850)]
Luminous Flux	2,100 lm
Color Designation	TL850
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	25 W
Mechanical and Housing	
Bulb Shape	T-8 (T8)

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	1.7 mg
Product Data	
Order product name	F25T8/TL850 ALTO 30PK
Full product name	F25T8/TL850 ALTO 30PK
Order code	280925
Material Nr. (12NC)	927851085002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677280925
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677280920

T8 Standard

Dimensional drawing

Product
F25T8/TL850 ALTO 30PK

