



T8 Plus

F25T8/TL830/PLUS/ALTO 30PK

Philips PLUS T8 lamps are energy-efficient lighting solutions and offer long life.

Product data

General Information	
Base	G13 [Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	42000 h
Life 12-Hr Instant Start [Hrs]	36000 h
Life 3-Hr Program Start [Hrs]	36000 h
Life 3-Hr Instant Start [Hrs]	30000 h
Features	ALTO® Plus
Light Technical	
Color Code	TL830 [CCT of 3000K (830)]
Initial lumen (Nom)	2150 lm
Color Designation	TL830
Design Mean Lumens	2045 lm
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	85
Operating and Electrical	
Power (Rated) (Nom)	25 W

Mechanical and Housing	
Cap-Base Information	Green Base
Nominal Length (Inch)	36
Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	28 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg

Product Data	
Order product name	F25T8/TL830/PLUS/ALTO 30PK
EAN/UPC - Product	046677280970
Order code	280974
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927851183002
Net Weight (Piece)	0.102 kg


Warnings and Safety

T8 Plus

Dimensional drawing

Product

F25T8/TL830/PLUS/ALTO 30PK



F25T8/830 36 ALTO Plus ES

