



T8 Plus

F25T8/TL841/PLUS/ALTO 30PK

Philips PLUS T8 lamps are energy-efficient lighting solutions and offer long life.

Product data

General Information		Mechanical and Housing	
Base	G13 [Medium Bi-Pin Fluorescent]	Cap-Base Information	Green Base
Life 12-Hr Programstart [Hrs]	42000 h	Nominal Length (Inch)	36
Life 12-Hr Instant Start [Hrs]	36000 h		
Life 3-Hr Program Start [Hrs]	36000 h	Approval and Application	
Life 3-Hr Instant Start [Hrs]	30000 h	Energy Saving Product	Energy Saving
Features	ALTO® Plus	Picogram Per Lumen Hour	28 pg/lm.h
		Mercury (Hg) Content (Nom)	1.7 mg
Light Technical		Product Data	
Color Code	TL841 [CCT of 4100K (841)]	Order product name	F25T8/TL841/PLUS/ALTO 30PK
Initial lumen (Nom)	2150 lm	EAN/UPC - Product	046677280994
Color Designation	TL841	Order code	280990
Design Mean Lumens	2045 lm	Numerator - Quantity Per Pack	1
Correlated Color Temperature (Nom)	4100 K	Numerator - Packs per outer box	30
Color Rendering Index (Nom)	85	Material Nr. (12NC)	927851184102
Operating and Electrical		Net Weight (Piece)	0.102 kg
Power (Rated) (Nom)	25 W		


Warnings and Safety

T8 Plus

Dimensional drawing

Product

F25T8/TL841/PLUS/ALTO 30PK



F25T8/841 36 ALTO Plus ES

