



# T8 Plus

## F32T8/TL841 PLUS ALTO HV 30PK

Philips PLUS T8 lamps are energy-efficient lighting solutions and offer long life.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	44000 h
Life 12-Hr Instant Start [Hrs]	36000 h
Life 3-Hr Program Start [Hrs]	38000 h
Life 3-Hr Instant Start [Hrs]	30000 h
Features	ALTO® Plus
Footnotes Fluorescent/CFL 1	Circle E- The encircled E means this bulb meets Federal minimum efficiency standards.

Light Technical	
Color Code	TL841 [ CCT of 4100K (841)]
Luminous Flux (Nom)	2950 lm
Color Designation	TL841
Design Mean Lumens	2800 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	85

Operating and Electrical	
Power (Rated) (Nom)	32 W

Mechanical and Housing	
Cap-Base Information	Green Base
Nominal Length (Inch)	48

  

Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	20 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg

Product Data	
Order product name	F32T8/TL841 PLUS ALTO HV 30PK
EAN/UPC - Product	046677281793
Order code	281790
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927852084104
Net Weight (Piece)	0.136 kg

# T8 Plus

## Dimensional drawing

### Product

F32T8/TL841 PLUS ALTO HV 30PK



F32T8/841 48 ALTO Plus ES

