



# Energy Advantage T8

## F32T8/ADV841/XEW/ALTO 25W 30PK

Philips Energy Advantage T8 lamps offer high energy savings without sacrificing performance.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	44000 h
Life 12-Hr Instant Start [Hrs]	38000 h
Life 3-Hr Program Start [Hrs]	38000 h
Life 3-Hr Instant Start [Hrs]	32000 h
Features	ALTO® (ALTO)

Light Technical	
Color Code	Advantage 841 [ CCT of 4100K (842)]
Luminous Flux (Nom)	2500 lm
Color Designation	Advantage 841
Design Mean Lumens	2425 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	85

Operating and Electrical	
Power (Rated) (Nom)	25 W

Mechanical and Housing	
Cap-Base Information	Green Base
Nominal Length (Inch)	48

Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	29 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg

Product Data	
Order product name	F32T8/ADV841/XEW/ALTO 25W 30PK
EAN/UPC - Product	046677280789
Order code	280784
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927852384203
Net Weight (Piece)	0.001 kg


### Warnings and Safety

# Energy Advantage T8

## Dimensional drawing

### Product

F32T8/ADV841/XEW/ALTO 25W 30PK



F32T8 25W/842 XEW ALTO ES

