



Energy Advantage T8

F32T8/ADV850/XEW/ALTO 25W 30PK

Philips Energy Advantage T8 lamps offer high energy savings without sacrificing performance.

Product data

General Information	
Base	G13 [Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	44000 h
Life 12-Hr Instant Start [Hrs]	38000 h
Life 3-Hr Program Start [Hrs]	38000 h
Life 3-Hr Instant Start [Hrs]	32000 h
Features	ALTO® (ALTO)

Light Technical	
Color Code	Advantage 850 [CCT of 5000K]
Initial lumen (Nom)	2400 lm
Color Designation	Advantage 850
Design Mean Lumens	2330 lm
Correlated Color Temperature (Nom)	5000 K
Color Rendering Index (Nom)	82

Operating and Electrical	
Power (Rated) (Nom)	25 W

Mechanical and Housing	
Cap-Base Information	Green Base
Nominal Length (Inch)	48

Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	30 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg

Product Data	
Order product name	F32T8/ADV850/XEW/ALTO 25W 30PK
EAN/UPC - Product	046677280796
Order code	280792
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927852385103
Net Weight (Piece)	0.001 kg


Warnings and Safety

Energy Advantage T8

Dimensional drawing

Product

F32T8/ADV850/XEW/ALTO 25W 30PK



F32T8 25W/851 XEW ALTO ES

