



U-Bent Rapid Start T8

FB32T8/TL841/6 ALTO 20PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

General Information		Nominal Length (Inch)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		22.44
Life 3-Hr Start [Hrs]	20000 h	Approval and Application	
Features	ALTO® (ALTO)	Energy Saving Product	Energy Saving
Light Technical		Picogram Per Lumen Hour	59 pg/lm.h
Color Code	TL841 [CCT of 4100K (841)]	Mercury (Hg) Content (Nom)	3.0 mg
Luminous Flux (Nom)	2800 lm	Product Data	
Color Designation	TL841	Order product name	FB32T8/TL841/6 ALTO 20PK
Design Mean Lumens	2535 lm	EAN/UPC - Product	046677379025
Correlated Color Temperature (Nom)	4100 K	Order code	379024
Color Rendering Index (Nom)	85	Numerator - Quantity Per Pack	1
Operating and Electrical		Numerator - Packs per outer box	20
Power (Rated) (Nom)	32 W	Material Nr. (12NC)	927860084102
Mechanical and Housing		Net Weight (Piece)	0.001 kg
Cap-Base Information	Green Base		

U-Bent Rapid Start T8

Dimensional drawing

Product

FB32T8/TL841/6 ALTO 20PK

FB32T8/6/841 22.44 ALTO ES

