



U-Bent Rapid Start T8

FB32T8/TL850/6 ALTO 20PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

General Information	
Base	G13 [Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	20000 h
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL850 [CCT of 5000K (850)]
Initial lumen (Nom)	2750 lm
Color Designation	TL850
Design Mean Lumens	2500 lm
Correlated Color Temperature (Nom)	5000 K
Color Rendering Index (Nom)	84
Operating and Electrical	
Power (Rated) (Nom)	32 W
Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	22.44
Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	60 pg/lm.h
Mercury (Hg) Content (Nom)	3.0 mg
Product Data	
Order product name	FB32T8/TL850/6 ALTO 20PK
EAN/UPC - Product	046677378806
Order code	378802
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	927860085003
Net Weight (Piece)	0.001 kg

Warnings and Safety

U-Bent Rapid Start T8

Dimensional drawing

Product

FB32T8/TL850/6 ALTO 20PK

FB32T8/6/850 22.44 ALTO ES

