



U-Bent Energy Advantage T8

FB32T8/ADV835/6/XEW/ALTO 25W

Philips Energy Advantage T8 25W U-Bent Lamps are environmentally responsible lamps, featuring energy savings and low mercury.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	Advantage 835 [CCT of 3500K]
Luminous Flux	2,400 lm
Color Designation	Advantage 835
Correlated Color Temperature (Nom)	3500 K
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	25 W
Mechanical and Housing	
Bulb Shape	T8-6U [U-bent T 8/8 inch with 6" spacing]

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	3.0 mg
Product Data	
Order product name	FB32T8/ADV835/6/XEW/ALTO 25W
Full product name	FB32T8/ADV835/6/XEW/ALTO 25W
Order code	204214
Material Nr. (12NC)	927860183601
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677204211
Numerator - Packs per outer box	20
EAN/UPC - Case	50046677204216

U-Bent Energy Advantage T8

Dimensional drawing

Product
FB32T8/ADV835/6/XEW/ALTO 25W

