



U-Bent Energy Advantage T8

FB32T8/ADV850/6/XEW/ALTO 25W

Philips Energy Advantage T8 25W U-Bent Lamps are environmentally responsible lamps, featuring energy savings and low mercury.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	Advantage 850 [CCT of 5000K]
Luminous Flux	2,350 lm
Color Designation	Advantage 850
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	25 W
Mechanical and Housing	
Bulb Shape	T8-6U [U-bent T 8/8 inch with 6" spacing]

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	3.0 mg
Product Data	
Order product name	FB32T8/ADV850/6/XEW/ALTO 25W
Full product name	FB32T8/ADV850/6/XEW/ALTO 25W
Order code	204248
Material Nr. (12NC)	927860185101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677204242
Numerator - Packs per outer box	20
EAN/UPC - Case	50046677204247

U-Bent Energy Advantage T8

Dimensional drawing

Product
FB32T8/ADV850/6/XEW/ALTO 25W

