



U-Bent Energy Advantage T8

FB32T8/ADV850/6/XEW/ALTO 25W

Philips Energy Advantage T8 25W U-Bent Lamps are environmentally responsible lamps, featuring energy savings and low mercury.

Product data

General Information	
Base	G13 [Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	20000 h
Features	ALTO® (ALTO)
Light Technical	
Color Code	Advantage 850 [CCT of 5000K]
Initial lumen (Nom)	2350 lm
Color Designation	Advantage 850
Design Mean Lumens	2280 lm
Correlated Color Temperature (Nom)	5000 K
Color Rendering Index (Nom)	85
Operating and Electrical	
Power (Rated) (Nom)	25 W
Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	22.44
Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	66 pg/lm.h
Mercury (Hg) Content (Nom)	3.0 mg

Product Data	
Order product name	FB32T8/ADV850/6/XEW/ALTO 25W
EAN/UPC - Product	046677204242
Order code	204248
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	927860185101
Net Weight (Piece)	0.001 kg

Warnings and Safety


• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

U-Bent Energy Advantage T8

Dimensional drawing

Product

FB32T8/ADV850/6/XEW/ALTO 25W



FB32T8/6 25W/851 XEW ALTO ES

