



# U-Bent Rapid Start T8

## FB31T8/TL835/ALTO 15/1

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

### Product data

General Information		Nominal Length (Inch)	
Base	G13 [ Medium Bi-Pin Fluorescent]		22.44
Life 3-Hr Start [Hrs]	24000 h	Approval and Application	
Features	ALTO® (ALTO)	Energy Saving Product	Energy Saving
		Mercury (Hg) Content (Nom)	3.0 mg
Light Technical		Product Data	
Color Code	TL835 [ CCT of 3500K (835)]	Order product name	FB31T8/TL835/ALTO 15/1
Initial lumen (Nom)	2750 lm	EAN/UPC - Product	046677226725
Color Designation	TL835	Order code	226720
Design Mean Lumens	2430 lm	Numerator - Quantity Per Pack	1
Correlated Color Temperature (Nom)	4100 K	Numerator - Packs per outer box	15
Color Rendering Index (Nom)	85	Material Nr. (12NC)	927861283502
Operating and Electrical		Net Weight (Piece)	0.001 kg
Power (Rated) (Nom)	31 W		
Mechanical and Housing			
Cap-Base Information	Green Base		

### Warnings and Safety

## U-Bent Rapid Start T8

### Dimensional drawing

**Product**

FB31T8/TL835/ALTO 15/1

FB31T8/TL835 ALTO® ES

