



U-Bent Rapid Start T8

FB29T8/TL835/EW/ALTO 15/1

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL835 [CCT of 3500K (835)]
Luminous Flux	2,550 lm
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	29 W
Mechanical and Housing	
Bulb Shape	T8-1-5/8U [U-bent T 1inch with 1-5/8" leg spacing]

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	3.0 mg
Product Data	
Order product name	FB29T8/TL835/EW/ALTO 15/1
Full product name	FB29T8/TL835/EW/ALTO 15/1
Order code	226761
Material Nr. (12NC)	927861383502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677226763
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677226768

U-Bent Rapid Start T8

Dimensional drawing

Product

FB29T8/TL835/EW/ALTO 15/1

