



U-Bent Rapid Start T8

FB29T8/TL835/EW/ALTO 15/1

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	24000 h
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL835 [CCT of 3500K (835)]
Luminous Flux (Nom)	2550 lm
Design Mean Lumens	2300 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	85
Operating and Electrical	
Power (Rated) (Nom)	29 W
Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	22.44
Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	3.0 mg
Product Data	
Order product name	FB29T8/TL835/EW/ALTO 15/1
EAN/UPC - Product	046677226763
Order code	226761
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	927861383502
Net Weight (Piece)	0.001 kg

U-Bent Rapid Start T8

Dimensional drawing

Product

FB29T8/TL835/EW/ALTO 15/1

FB29T8/TL835 EW ALTO® ES

